

Philips
Cordless phone answer
machine

SE7452B



Enhanced High Def Voice

Ultimate call clarity

Conversations have never been so life-like and voices so natural than with the outstanding sound clarity of the SE7 series. The sparkling color screen reflects the purity of the voice enhancement for the pleasure of your eyes and your ears

Outstanding sound quality

- Enhanced speakerphone for real-life handsfree conversations
- Unique acoustic design for superb call clarity
- Enhanced High Def Voice

All the features of DECT

- Virtually interference free
- Up to 100% greater battery life
- Ultra private calls

Superior Performance

- Digital answering machine
- Store up to 250 names-numbers in your phonebook
- SIM-card copying facility

PHILIPS
sense and simplicity

Specifications

Picture/Display

- Backlight
- Backlight color: White
- Main Display Resolution: 128x128 pixel
- Main Display Technology: CSTN

Sound

- Handset ringers: Polyphonic
- Volume Control: Volume Control up/down

Convenience

- Alarms: Alarm Clock
- Base Station keys: Answering machine keys, Paging key
- Base Station Mem. Card Reader: SIM Card Reader
- Battery charging indication
- Call Management: Call Waiting, Caller ID, Microphone mute
- Ease of Use: Graphical User Interface, Keypad Lock, Menu Control
- Function: Babysit function, Baby Call
- Multi base capability: 4
- Multi handset capability: Up to 5 handsets
- Personalisation/Customization: Wallpaper
- Signal strength indication
- VIP group with own melody: Yes (3 groups)
- Backlit keypad: Yes (White)
- Speakerphone-Talk handsfree

Network Features

- Antenna: Integrated on base, Integrated on

handset

- Compatible: GAP
- Dialing: Tone, Pulse

Operator Requirements

- Name and Caller ID
- Caller ID on call waiting

Answering Machine

- Plug & Play Answering machine
- Recording time capacity: Up to 30 min.
- Message counter on base

Memory Capacity

- Call log entries: 50
- Phonebook: 250

Dimensions

- Base dimensions: 140.5 x 90 x 92 mm
- Handset dimensions: 162.4 x 46.5 x 29.8 mm

Power

- Battery capacity: 750 mAh
- Battery type: AAA NiMH
- Kind of Battery: Rechargeable
- Mains power: AC 120V - 60Hz
- Number of batteries: 2 per handset
- Standby time: 150 hours
- Talk time: Up to 12 hours

Product highlights

Virtually interference free

Thanks to an advanced digital technology, calls are undisturbed by interferences from other devices.

Enhanced speakerphone

Combine a high quality speaker, sophisticated signal processing, a real acoustic chamber and full duplex handsfree and you'll get the most natural reproduction of a conversation. Both sides can speak and be heard at the same time, like in a face-to-face conversation.

Unique acoustic design

Our unique acoustic design provides a high-quality, rich communication experience. A best-in-class system designed for superb call clarity.

Enhanced Hi Def Voice

Enjoy high quality conversation, with a level of clarity rarely heard before. Thanks to a high-quality speaker, sophisticated technology and to a real acoustic chamber, the audio spectrum reaches far beyond what's normally heard on a telephone.

SIM-card copying facility

With the SIM-card copying facility, you can transfer your whole mobile-phonebook on to your home telephone in a matter of seconds.



Issue date 2007-10-03

Version: 3.0

12 NC: 8670 000 28553
UPC: 6 09585 12926 9

© 2007 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips
Electronics N.V. or their respective owners.

www.philips.com